

SISTEMA DE INSPECCIÓN DE VÍDEO SEESNAKE MICROREEL



SKU: N / A | **Categorías:** [Carretes y cámaras](#), [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección por vídeo de desagüe y alcantarillado](#), [Inspección Y Localización](#) | **Etiquetas:** [Ridgid](#)

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [tabbed_section style="default" alignment="left"] [/vc_column] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [vc_column_text]

Sistema de inspección de vídeo SeeSnake® microReel

Tuberías de 1-1/2" a 4 / 5" (40 a 100 / 125 mm)* hasta 100 pies (30 m). Supera codos de 90° en casi todas las tuberías de 2" (50 mm).

El sistema de inspección de vídeo microReel proporciona maniobrabilidad y tamaño reducido para inspección de conductos de pequeño diámetro y curvas cerradas.

* 4" (100 mm) cuando se utiliza con una cámara de inspección microEXPLORER™ o micro CA-300. 5" (125 mm) cuando se utiliza con un monitor SeeSnake.

[/vc_column_text] [/vc_column] [/vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]

[/vc_column] [/vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [tabbed_section style="default"]

alignment="left"][/tabbed_section][[/vc_column][[/vc_row]

COTECNO

COTECNO