

TRANSMISOR DE LÍNEAS NAVITRACK - 10 W



SKU: N / A | **Categorías:** [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Localización de tuberías y/o líneas](#) | **Etiquetas:** [Ridgid](#)

DESCRIPCIÓN DEL PRODUCTO

Transmisor de líneas NaviTrack - 10 W

```
[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]
```

```
[/vc_column] [/vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [tabbed_section style="default" alignment="left"] [/tabbed_section] [/vc_column] [/vc_row]
```

COTECNO