

TRANSMISOR REMOTO (SONDA DE 512 HZ)



SKU: N / A | **Categorías:** [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Localización de tubería sanitaria](#) | **Etiquetas:** [Ridgid](#)

DESCRIPCIÓN DEL PRODUCTO

Transmisor remoto (sonda de 512 Hz)

```
[/vc_column_text][vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle"
scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-
extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default"
column_border_width="none" column_border_style="solid"]
```

```
[/vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center"
text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default"
column_border_width="none" column_border_style="solid"][tabbed_section style="default"
alignment="left"][/tabbed_section][/vc_column][vc_row]
```

COTECNO