

SENSORES COMBINADOS



SKU: N / A | **Categorías:** [Thies Clima](#), [Viento](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Los sensores combinados ofrecen, según su diseño, estaciones meteorológicas muy compactas. Los siguientes parámetros se pueden medir, visualizar o transmitir de forma remota. Según el modelo:

Las aplicaciones típicas son:

- Meteorología
- Medición ambiental
- Técnica de
- Control Sistema de control de edificios
- Ingeniería de tráfico
- Tecnología de invernadero

Muestra de parámetros medidos:

- Velocidad del
- Viento Dirección del viento
- Intensidad de
- Precipitación Tipo de precipitación
- Brillo Temperatura
- Crepuscular
- Humedad
- Relativa
- Presión atmosférica barométrica
- Radiación global

[/vc_column_text] [vc_row_inner column_margin="default" text_align="left" css=".vc_custom_1597668708409{border-radius: 2px !important;}"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Imagen

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Nombre del Producto

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Descripción corta

[/vc_column_text] [/vc_column_inner] [/vc_row_inner] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138423" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado

4.3324.32.000 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.

Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión estándar
- Velocidad del viento: salida de frecuencia
- Dirección del viento: paralelo de 8 bits

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-2/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138453" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Transmisor de viento combinado

4.3324.32.001 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Modelo con salidas digitales.

Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento de la

- Versión de barco de flujo de aire horizontal
- Velocidad del viento de salida: salida de frecuencia
- Dirección del viento de salida: paralelo de 8 bits

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-5/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138455" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de viento combinado

4.3324.32.xxx[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión estándar
- Velocidad del viento: salida analógica
- Dirección del viento: salida analógica

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-6/"][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138456" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Transmisor de viento combinado

```
4.3329.00.510[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]Transmisor de medida para medir la velocidad del viento, la dirección del viento y la temperatura del aire.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-7/"][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]
```

Transmisor de viento combinado

```
4.3336.22.000[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]Modelo con salidas digitales.  
Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal
```

- Versión estándar
- Velocidad del viento: salida de frecuencia
- Dirección del viento: sincronismo serial

```
[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-3/"][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]
```

Transmisor de viento combinado

4.3336.32.001[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]Modelo con salidas digitales.

Transmisor de valores de medición para la medición de la velocidad del viento y la dirección del viento del flujo de aire horizontal

- Versión de barco
 - Velocidad del viento: salida de frecuencia
 - Dirección del viento: sincronización en serie

[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-de-viento-combinado-4/"][/vc_column_inner][/vc_row_inner]

```
[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]
```

Estación meteorológica Compact WSC11

4.9056.10.000[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]La estación meteorológica Compact WSC11 está diseñada para su uso en la automatización de edificios
(por ejemplo, control de sombras)[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/estacion-meteorologica-compact-wsc11/"] [/vc_column_inner] [/vc_row_inner]

```
[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"]
```

tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Estación meteorológica Compact WSC11

4.9056.30.000 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] La estación meteorológica Compact WSC11 está diseñada para su uso en la automatización de edificios (por ejemplo, control de sombras). Con receptor alternativo RDS / DAB +. [/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"] url="http://test.cotecno.cl/nuestros-productos/estacion-meteorologica-compact-wsc11-2/" [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="138434" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Sensor de clima D

4.91xx.00.061 [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] El sensor de clima D sirve para la medición de datos ambientales.

Hay modelos disponibles para medir:

- Velocidad del viento
- Precipitación
- Brillo
- Crepúsculo
- Temperatura del aire
- Rel. Humedad

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"] url="http://test.cotecno.cl/nuestros-productos/sensor-de-clima-d/" [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

```
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none" [image_with_animation image_url="138455" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none" [vc_column_text]
```

Sensor de clima EE. UU.

4.920x.x0.00x [/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none" [vc_column_text] El CLIMA SENSOR US sirve para la medición de parámetros
ambientales. Están disponibles para su posterior procesamiento como

- telegrama en serie a través de RS485 / 422
y / o como
- señales analógicas a través de salidas de tensión

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/sensor-de-clima-us/"] [/vc_column_inner] [/vc_row_inner]

[/vc_column] [/vc_row]

COTECNO