

TWINFILTER



SKU: N / A | **Categorías:** [Filtración HiFlux](#) |

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center"
text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom"
bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none"
column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default"
phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-
Color"][/tabbed_section][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-
extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

[Bolsas de filtro](#)

```
[/vc_column_text][image_with_animation image_url="159414" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

[Cartuchos Texflow](#)

```
[/vc_column_text][image_with_animation image_url="159417" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

[Cartuchos Pleatflow](#)

```
[/vc_column_text][image_with_animation image_url="159416" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_row_inner][vc_column_text]
```

- Descripción general de las bolsas filtrantes TwinFilter
- Descripción general TwinFilter Texflow
- Resumen TwinFilter Pleatflow TH

```
[/vc_column_text][vc_column][vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO